

appliances for drinking water at its best

BRAVO DP DIRECT

Filter cartridge



Filter housings made in PET, a highly recyclable plastic, are manufactured with a proprietary procedure saving up to 60% of energy in injection molding compared with standard plastics. That is one of Atlas Filtri commitments to comply with Kyoto Treaty for the reduction of green house gas (CO₂) emissions in the atmosphere.

COMPANY WITH QUALITY MANAGEMENT
SYSTEM CERTIFIED BY DNV
= ISO 9001:2008 =



▶▶▶▶▶ more to drink

BRAVO DP-Direct

undersink filters for drinking water at its best
with direct connection to main faucet

BRAVO DP-Direct performs Patented and Registered Model Housings. Thanks to the single head design, BRAVO DP-Direct Duo and Trio have no need for connections nor fittings in between the housings, no work for connections and no risk of leaking. The housing head is stronger and more reliable than ever. In addition, thanks to the design, the width is dramatically reduced **saving space for the installation.**

MAX WORKING PRESSURE 8 BAR

MAX WORKING TEMPERATURE 45°C



HOUSING MONO
REGISTERED MODEL
SPACE SAVING

Model	Cartridges assortment	flow l/m
BRAVO DP-Direct MONO BT	BT PP LA 5 mcr	6
BRAVO DP-Direct MONO CB	CB 5 mcr	6
BRAVO DP-Direct MONO AB	AB 0,45 mcr	4
BRAVO DP-Direct MONO CASE	CA-SE 0,3 mcr	4
BRAVO DP-Direct MONO HF	CA-SE HF 0,15 mcr	6

Model	Cartridges assortment	flow l/m
BRAVO DP-Direct DUO FA-LA	FA 5 mcr + LA	6
BRAVO DP-Direct DUO FA-CB	FA 5 mcr + CB 5 mcr	6
BRAVO DP-Direct DUO FA-AB	FA 5 mcr + AB 0,45 mcr	4
BRAVO DP-Direct DUO FA-CASE	FA 5 mcr + CA-SE 0,3 mcr	4
BRAVO DP-Direct DUO FA-HF	FA 5 mcr + CA-SE HF 0,15 mcr	6
BRAVO DP-Direct DUO PP-LA	PP 5 mcr + LA	6
BRAVO DP-Direct DUO PP-CB	PP 5 mcr + CB 5 mcr	6
BRAVO DP-Direct DUO PP-AB	PP 5 mcr + AB 0,45 mcr	4
BRAVO DP-Direct DUO PP-CASE	PP 5 mcr + CA-SE 0,3 mcr	4
BRAVO DP-Direct DUO PP-HF	PP 5 mcr + CA-SE HF 0,15 mcr	6




HOUSING DUO
REGISTERED MODEL
PATENT PENDING
SPACE SAVING



HOUSING TRIO
REGISTERED MODEL
PATENT PENDING
SPACE SAVING

Model	Cartridges assortment	flow l/m
BRAVO DP-Direct TRIO FA-CB-AB	FA 5 mcr + CB 5 mcr + AB 0,45 mcr	4
BRAVO DP-Direct TRIO FA-LA-CASE	FA 5 mcr + LA + CA-SE 0,3 mcr	4
BRAVO DP-Direct TRIO FA-LA-HF	FA 5 mcr + LA + CA-SE HF 0,15 mcr	6
BRAVO DP-Direct TRIO FA-CB-HF	FA 5 mcr + CB 5 mcr + CA-SE HF 0,15 mcr	6
BRAVO DP-Direct TRIO PP-CB-AB	PP 5 mcr + CB 5 mcr + AB 0,45 mcr	4
BRAVO DP-Direct TRIO PP-LA-CASE	PP 5 mcr + LA + CA-SE 0,3 mcr	4
BRAVO DP-Direct TRIO PP-LA-HF	PP 5 mcr + LA + CA-SE HF 0,15 mcr	6
BRAVO DP-Direct TRIO PP-CB-HF	PP 5 mcr + CB 5 mcr + CA-SE HF 0,15 mcr	6

Flow rate in litres per minute (l/m) is the average water flow from the dedicated tap (filtered water) using a new cartridge. The flow rate may vary in function of water quality and time in service (life-span) of the cartridges. Life-span is the average working life of the cartridge. It depends on the water quality, which is an extremely variable factor: life-span is indicated for a mains water supply with average european characteristics. BRAVO DP are not potable water-makers: control the water quality before installation.



BRAVO DP-Direct undersink filters have been designed for the production of good and pure water directly at the point of use. The filters can be easily installed under the kitchen sink, thanks to the complete set of accessories, with saving of space.


The filters are supplied with a special connection kit that allows the **direct connection** to the main faucet: there is no need of making holes on the sink counter. All the cold water is purified and can be used for drinking, cooking and preparing of foods and drinks.

BRAVO DP-Direct are made of completely non-toxic materials and are suitable to the use with drinking water, in compliance with the most stringent EU directives.









accessories included



accessories available



cartridges assortment

 <p>FA 5 micron SEDIMENT. Wound polypropylene filter. Filtration of sand, scales, lime, rust, fine particles. Life-span: 3-6 months.</p>	 <p>PP/CPP 5 micron SEDIMENT. Melt-blown polypropylene grooved (PP) or smooth (CPP) filter: high efficiency filtration of fine particles, rust, lime, sand, scales. Life-span: 3-6 months.</p>	 <p>BT PP LA 5 micron SEDIMENT G.A.C. Melt-blown polypropylene filter and Granular Activated Carbon. Filtration of fine particles, rust, lime, sand, scales; reduction of chlorine (bad tastes, odours) and chloride pollutants (pesticides, solvents, etc). Life-span: 3 months.</p>	 <p>LA CARBON G.A.C. Container with Granular Activated Carbon. Reduction of chlorine (bad tastes, odours) and chloride pollutants (pesticides, solvents, etc). Life-span: 3 months.</p>
 <p>AB 0,45 micron CERAMIC. Filtration of very fine particles and some micro-organisms. Life-span: 6-12 months. Maintenance: surface scraping every 2-3 months.</p>	 <p>CB 5 micron CARBON BLOCK. Filtration of fine particles (rust, lime, sand, scales); reduction of chlorine (bad tastes, odours) and chloride pollutants (pesticides, solvents, etc). Life-span: 3-6 months.</p>	 <p>CA-SE 0,3 micron CARBON BLOCK. Filtration of very fine particles and some micro-organisms; reduction of chlorine (bad tastes, odours) and chloride pollutants (pesticides, solvents, etc). Life-span: 6-12 months. Maintenance: surface scraping every 2-3 months.</p>	 <p>CA-SE HF 0.15 micron CARBON BLOCK. Microfiltration with "hollow-fibre" capillary membranes (STER-O-TAP®) of very fine particles and some micro-organisms; reduction of chlorine (bad tastes, odours) and chloride pollutants (pesticides, solvents, etc). Life-span: 6 months. Maintenance: surface scraping every 2-3 months.</p>

cartridge variants

Cartridges available on demand


- GAC-Ag** Granular Activated Carbon Silver treated.
- QA-AF** Anti-nitrate ionic exchange resin.
- KDF** Heavy-metals and chlorine reduction medium.
- OT** Arsenic reduction medium.
- CA-SE HF-U** Carbon block with "hollow-fibre" ultra-filtration element at 0,02 micron.

Cartridges with double O-ring quick-fit system **BX**.



BRAVO DP-Direct housings fit to **BX** and standard **SX** (DOE) cartridges.

INSTALLATION SCHEME



SPARE PARTS FOR KIT BRAVO DP-Direct

